



### PRODUCT INFORMATION

DuPont™ Tyvek® 500 Labcoat with zipper model PL309NP. Stitched internal seams. Collar. Zipper. Without pockets. Elasticated cuffs (tunnelled). White.

### ATTRIBUTES

Full Part Number	TYPL39SWHNP
Fabric/Materials	TYVEK®
Design	Labcoat with elastics and zipper
Seam	Stitched (internal)
Color	White
Sizes	SM, MD, LG, XL, 2X
Quantity/Box	50 per box, bulk packed.

### FEATURES

- Certified according to Regulation (EU) 2016/425.
- Partial body chemical protective clothing, Category III, Type PB [6-B].
- EN 14126 (barrier to infective agents)
- Antistatic treatment (EN 1149-1) - on both sides; see footnotes

### SIZETABLE

PRODUCT SIZE	ARTICLE NUMBER	ADDITIONAL INFO
SM	D15534010	
MD	D15534011	
LG	D15534012	
XL	D15534013	
2X	D15534014	

### PHYSICAL PROPERTIES

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Abrasion Resistance <sup>7</sup>	EN 530 Method 2	>100 cycles	2/6 <sup>1</sup>
Basis Weight	DIN EN ISO 536	41.5 g/m <sup>2</sup>	N/A
Colour.	N/A (598)	White	N/A
Exposure to high Temperature	N/A (598)	Melting point ~135 °C	N/A
Flex Cracking Resistance <sup>7</sup>	EN ISO 7854 Method B	>100000 cycles	6/6 <sup>1</sup>
Puncture Resistance	EN 863	>10 N	2/6 <sup>1</sup>
Resistance to water penetration	AATCC 127	>10 kPa	N/A
Surface Resistance at RH 25%, inside <sup>7</sup>	EN 1149-1	< 2,5 · 10 <sup>9</sup> Ohm	N/A
Surface Resistance at RH 25%, outside <sup>7</sup>	EN 1149-1	< 2,5 · 10 <sup>9</sup> Ohm	N/A
Tensile Strength (MD)	DIN EN ISO 13934-1	>30 N	1/6 <sup>1</sup>
Tensile Strength (XD)	DIN EN ISO 13934-1	>30 N	1/6 <sup>1</sup>
Trapezoidal Tear Resistance (MD)	EN ISO 9073-4	>10 N	1/6 <sup>1</sup>

## TECHNICAL DATA SHEET

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Trapezoidal Tear Resistance (XD)	EN ISO 9073-4	>10 N	1/6 <sup>1</sup>

1 According to EN 14325 | 2 According to EN 14126 | 3 According to EN 1073-2 | 4 According to EN 14116 | 12 According to EN 11612 | 5 Front Tyvek® / Back |  
 6 Based on test according to ASTM D-572 | 7 See Instructions for Use for further information, limitations and warnings | > Larger than | < Smaller than |  
 <= Smaller than or equal to | N/A Not Applicable | STD DEV Standard Deviation |

### GARMENT PERFORMANCE

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Seam Strength	EN ISO 13935-2	>50 N	2/6 <sup>1</sup>
Shelf Life <sup>7</sup>	N/A (598)	10 years <sup>6</sup>	N/A
Type PB 6: Partial Body Protection	EN 13034	Pass	N/A

1 According to EN 14325 | 3 According to EN 1073-2 | 12 According to EN 11612 | 13 According to EN 11611 | 5 Front Tyvek® / Back |  
 6 Based on test according to ASTM D-572 | 7 See Instructions for Use for further information, limitations and warnings |  
 11 Based on the average of 10 suits, 3 activities, 3 probes | > Larger than | < Smaller than | <= Smaller than or equal to | N/A Not Applicable |  
 \* Based on lowest single value |

### COMFORT

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Air Permeability (Gurley method)	TAPPI T460	< 45 s	N/A

2 According to EN 14126 | 5 Front Tyvek® / Back | > Larger than | < Smaller than | <= Smaller than or equal to | N/A Not Applicable |

### PENETRATION AND REPELLENCY

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Repellency to Liquids, Sodium Hydroxide (10%)	EN ISO 6530	>95 %	3/3 <sup>1</sup>
Repellency to Liquids, Sulphuric Acid (30%)	EN ISO 6530	>95 %	3/3 <sup>1</sup>
Resistance to Penetration by Liquids, Sodium Hydroxide (10%)	EN ISO 6530	<1 %	3/3 <sup>1</sup>
Resistance to Penetration by Liquids, Sulphuric Acid (30%)	EN ISO 6530	<1 %	3/3 <sup>1</sup>

1 According to EN 14325 | > Larger than | < Smaller than | <= Smaller than or equal to |

### BIOLOGICAL BARRIER

PROPERTY	TEST METHOD	TYPICAL RESULT	EN
Resistance to Penetration by Biologically Contaminated Aerosols	ISO/DIS 22611	Pass	1/3 <sup>2</sup>
Resistance to Penetration by Blood and Body Fluids using Synthetic Blood	ISO 16603	3,5 kPa	3/6 <sup>2</sup>
Resistance to Penetration by Blood-borne Pathogens using Bacteriophage Phi-X174	ISO 16604	Pass	2/6 <sup>2</sup>
Resistance to Penetration by Contaminated Liquids	EN ISO 22610	<= 15 min	1/6 <sup>2</sup>
Resistance to Penetration by Contaminated Solid Particles	ISO 22612	Pass	1/3 <sup>2</sup>

1 According to EN 14325 | > Larger than | < Smaller than | <= Smaller than or equal to |

### PERMEATION DATA DUPONT™ TYVEK® 500 ACCESSORY

HAZARD / CHEMICAL NAME	PHYSICAL STATE	CAS	BT ACT	BT 0.1	BT 1.0	EN	SSPR	M DPR	CUM 480	TIME 150	ISO
Sodium hydroxide (40%)	Liquid	1310-73-2	>240	>240	>240	5	<0.04	0.04	<20	>240	5
Sulfuric acid (18%)	Liquid	7664-93-9	>480	>480	>480	6	<0.04	0.04	<20	>480	6
Sulfuric acid (30%)	Liquid	7664-93-9	>240	>240	>240	5	<0.04	0.04	<20	>240	5



BTAct (Actual) Breakthrough time at MDPR [mins] | BT0.1 Normalized breakthrough time at 0.1  $\mu\text{g}/\text{cm}^2/\text{min}$  [mins] |

BT1.0 Normalized breakthrough time at 1.0  $\mu\text{g}/\text{cm}^2/\text{min}$  [mins] | EN Classification according to EN 14325 | SSPR Steady state permeation rate [ $\mu\text{g}/\text{cm}^2/\text{min}$ ] |

MDPR Minimum detectable permeation rate [ $\mu\text{g}/\text{cm}^2/\text{min}$ ] | CUM480 Cumulative permeation mass after 480 mins [ $\mu\text{g}/\text{cm}^2$ ] |

Time150 Time to reach cumulative permeation mass of 150  $\mu\text{g}/\text{cm}^2$  [mins] | ISO Classification according to ISO 16602 |

CAS Chemical abstracts service registry number | min Minute | > Larger than | < Smaller than | imm Immediate (< 10 min) | nm Not tested |

sat Saturated solution | N/A Not Applicable | na Not attained | GPR grade General purpose reagent grade | \* Based on lowest single value |

8 Actual breakthrough time; normalized breakthrough time is not available | DOT5 Degradation after 5 min | DOT30 Degradation after 30 min |

DOT60 Degradation after 60 min | DOT240 Degradation after 240 min | BT1383 Normalized breakthrough time at 0.1  $\mu\text{g}/\text{cm}^2/\text{min}$  [mins] acc. ASTM F1383 |

### Important Note

The permeation data published have been generated for DuPont by independent accredited testing laboratories according to the test method applicable at that time (EN ISO 6529 (method A and B), ASTM F739, ASTM F1383, ASTM D6978, EN369, EN 374-3) The data is typically the average of three fabrics samples tested. All chemicals have been tested at an assay of greater than 95 (w/w) % unless otherwise stated. The tests were performed between 20 °C and 27 °C and at

environmental pressure unless otherwise stated. A different temperature may have significant influence on the breakthrough time. Permeation typically increases with temperature. Cumulative permeation data have been measured or have been calculated based on minimum detectable permeation rate. Cytostatic drugs testing has been performed at a test temperature of 27°C according to ASTM D6978 or ISO 6529 with the additional requirement of reporting a normalized breakthrough time at 0.01 µg/cm<sup>2</sup>/min. Chemical warfare agents (Lewisite, Sarin, Soman, Mustard, Tabun and VX Nerve Agent) have been tested according to MIL-STD-282 at 22°C or according to FINABEL 0.7 at 37°C. Permeation data for Tyvek® is applicable to white Tyvek® 500 and Tyvek® 600 only and is not applicable for other Tyvek® styles or colours. Permeation data are usually measured for single chemicals. The permeation characteristics of mixtures can often deviate considerably from the behaviour of the individual chemicals. The permeation data for gloves published have been generated according to ASTM F739 and to ASTM F1383. The degradation data for gloves published have been generated based on a gravimetric method. This degradation testing exposes one side of the glove material to the test chemical for four hours. The percent weight change after exposure is measured at four time intervals: 5, 30, 60 and 240 minutes.

The information provided herein corresponds to our knowledge on the subject at the date of its publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.

### Degradation Ratings:

- E: EXCELLENT (0-10% Weight Change)
- G: GOOD (11-20% Weight Change)
- F: FAIR (21-30% Weight Change)
- P: POOR (31-50% Weight Change)
- NR: NOT RECOMMENDED (Above 50% Weight Change)
- NT: NOT TESTED

Degradation is the physical change in a material after chemical exposure. Typical observable effects may be swelling, wrinkling, deterioration, or delamination. Strength loss may also occur.

Please use the permeation data provided as a part of the risk assessment to assist with the selection of a protective fabric, garment, glove or accessory suitable for your application. Breakthrough time is not the same as safe wear time. Breakthrough times are indicative of the barrier performance, but results can vary between the test methods and laboratories. Breakthrough time alone is insufficient to determine how long a garment may be worn once the garment has been contaminated. Safe user wear time may be longer or shorter than the breakthrough time depending on the permeation behaviour of the substance, the toxicity of the substance, working conditions and the exposure conditions (e.g. temperature, pressure, concentration, physical state).

Latest Update Permeation Data: 10/24/2022

### WARNING

The information provided herein corresponds to our knowledge on the subject at the date of its publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.

This garment and/or fabric are not flame resistant and should not be used around heat, open flame, sparks or in potentially flammable environments.

Working in Ex-Zones: Please take this into account for your risk-assessment that the attached socks may isolate the wearer. There is the possibility that the garment and wearer cannot be grounded via the shoes and other measures for grounding the garment and the wearer are required

### DuPont™ SafeSPEC™ - We're here to help

Our powerful web-based tool can assist you with finding the appropriate DuPont garments for chemical and controlled environment hazards.



DuPont Personal Protection  
SafeSPEC™

DuPont Personal Protection

DuPont Personal Protection

CREATED ON: OCTOBER 7, 2024